


**PRODUCT – CODE**



<b>A....TYPE OF PRODUCT</b>	32L- SHUT OFF BIOTECH VALVE 33- SAMPLING VALVE 34- CHECK VALVE 36- DIAPHRAGM VALVE, CAST 46- PRESSURE RELIEF VALVE 52- BULLS-EYE SIGHTGLASS 54Y- Y-STRAINER 54L- L-STRAINER 55Y- Y-STRAINER WITH SIGHTGLASS	32T- SHUT OFF BIOTECH VALVE 33A- SAMPLING VALVE-ASEPTIC 34A- AIR BLOW CHECK VALVE 43- BUTTERFLY VALVE 46A- PRESSURE RELIEF VALVE W/AIR OVER RIDE 53- IN-LINE SIGHTGLASS 53A- IN-LINE SIGHTGLASS (A-DESIGN for 0.5" – 1.5") 54I- IN-LINE STRAINER 55L- L-STRAINER WITH SIGHTGLASS
<b>B....NUMBER OF CONNECTIONS</b>	1- 1 CONNECTION 3- 3 CONNECTIONS	2- 2 CONNECTIONS 4- 4 CONNECTIONS
<b>C....TYPE OF CONNECTION</b>	F- FLANGE L- FLANGE W- BUTT WELD / WELD END	K- NPT-MALE P- CLAMP
<b>C....SIZE OF CONNECTIONS</b>	03- ¼ INCH 05- ½ INCH 10- 1 INCH 20- 2 INCH 30- 3 INCH 60- 6 INCH 100- 10 INCH	04- 3/8 INCH 07- ¾ INCH 15- 1 ½ INCH 25- 2 ½ INCH 40- 4 INCH 80- 8 INCH
<b>D....TYPE OF MATERIAL</b>	4- 304 STAINLESS 6L- 316L STAINLESS	6- 316 STAINLESS HC- HASTELLOY
<b>E....TYPE OF ELASTOMER</b>	E- EPDM S- SILICONE TV- TEFLON ENCAPSULATED VITON	N- BUNA-N T- TEFLON V- VITON
<b>F....SIGHTGLASS MTRL (If Applicable)</b>	AC- ACRYLIC	PY- PYREX
<b>G....MODE OF OPERATION or MESH SCREEN (If Applicable)</b>	M- MANUAL MP- MANUAL PLYER HANDLE AS- AIR-SPRING ACTUATOR M- MESH SCREEN	MI- MANUAL INFINITE ADJUSTABLE AA- AIR-AIR ACTUATOR SE- ELECTRIC ACTUATOR MW- MESH SCREEN WEDGE WIRE

SAMPLE: In-Line Sightglass in 316L Stainless Steel with 2 Inch T/C Connection, EPDM Elastomer and Pyrex Tube

**PART NO.: 53-2-P20-6L-E-PY**

SPARE PARTS: Refer to item in sectional drawing and product code